


TECHNICAL INFORMATION \_ CAT. N. YU## SOCL SOCL A1212

## COAXIAL SHUT OFF 90 VALVE 12 ON PIPE + SIP VALVE 12



Clean and Aseptic Valves of CAD Product Line have simple and safe design, with their full drainability, without asymptotic seal and dead leg, are offering fast cleanability and sterilization practices. They are designed to fulfil stringent demands of CIP-SIP and Production Cycles on Aseptic Processing.

**YU## - SOCL - SOCL - Coaxial Shut Off on Pipe Valves + SIP Valve** for SAFE areas designed to feed or take off fluids or gases from the process piping with Zero dead leg. The satellite valve may be used for CIP-SIP process of the Valve on Pipe body and their downstream pipeline. Body shape with flush flow seal on pipe and their internal design offer a very reliable component for Aseptic Processing Application. Standard version are short butt weld ends but, on demand, may be delivered for orbital welding or with Tri-Clamp connections.

CODE	A 1	A 2	B mm (inch)	C mm (inch)	D1 mm (inch)	D2 mm (inch)	E mm (inch)	F mm (inch)	G mm (inch)	H mm (inch)	TUBE 1* mm (inch)	TUBE 2* mm (inch)	TUBE 3* mm (inch)
YU12-SOCL-SOCL-A1212	M34x1	M34x1	26,00 (1,02)	12,00 (0,47)	5,00 (0,20)	5,00 (0,20)	8,00 (0,32)	52,00 (2,05)	19,00 (0,75)	31,50 (1,24)	12,70x1,65 (0,50x0,065)	12,70x1,65 (0,50x0,065)	12,70x1,65 (0,50x0,065)
YU19-SOCL-SOCL-A1212	M34x1	M34x1	26,00 (1,02)	15,00 (0,59)	5,00 (0,20)	5,00 (0,20)	8,00 (0,32)	52,00 (2,05)	15,50 (0,62)	31,50 (1,24)	12,70x1,65 (0,50x0,065)	19,50x1,65 (0,75x0,065)	12,70x1,65 (0,50x0,065)
YU25-SOCL-SOCL-A1212	M34x1	M34x1	26,00 (1,02)	18,50 (0,73)	5,00 (0,20)	5,00 (0,20)	8,00 (0,32)	52,00 (2,05)	18,50 (0,73)	31,50 (1,24)	12,70x1,65 (0,50x0,065)	25,40x1,65 (1,00x0,065)	12,70x1,65 (0,50x0,065)
YU38-SOCL-SOCL-A1212	M34x1	M34x1	26,00 (1,02)	24,50 (0,97)	5,00 (0,20)	5,00 (0,20)	8,00 (0,32)	52,00 (2,05)	25,00 (0,98)	31,50 (1,24)	12,70x1,65 (0,50x0,065)	38,10x1,65 (1,50x0,065)	12,70x1,65 (0,50x0,065)
YU50-SOCL-SOCL-A1212	M34x1	M34x1	31,00 (1,22)	31,00 (1,22)	5,00 (0,20)	5,00 (0,20)	8,00 (0,32)	52,00 (2,05)	31,00 (1,22)	31,50 (1,24)	12,70x1,65 (0,50x0,065)	50,80x1,65 (2,00x0,065)	12,70x1,65 (0,50x0,065)

(\*) US Tube ASTM® A269/270 – ASME BPE

### SPECIFICATION:

CAD SIZE	A12						
----------	-----	--	--	--	--	--	--

NET VOLUME <sup>(1)</sup>	ml	2,86					
---------------------------	----	------	--	--	--	--	--

<sup>(1)</sup> Internal valve cavity only, for each cavity, with diaphragm on site

MATERIAL	1,4435-BN2 - Low Ferrite - Low Sulphur
----------	--

**Design Temperature:** -80 to 200 °C (-112 to 392 °F)

**Application Areas:** SAFE

**Design Pressure, Valve Body:** -1 to 10 bar (-14.5 to 145 psi)

**Note:** The applied actuator and diaphragm may have different design temperature and/or pressure limits. The weakest component determines the maximum design temperature and pressure limits, when they are assembled.

**Surface Roughness:** Internal surface (manually polished)  $Ra \leq 0.3\mu m$  (16 $\mu in$ )  
External surface  $Ra \leq 0.5\mu m$  (20 $\mu in$ )

**Surface Treatment:** Available also on EP version - Eletropolishing after manual polished

**Labeling:** Each valve body is labeled for full LOT traceability

**Packaging:** Valve body is sealed in plastic bags and packaged in a closed box with Operating and Maintenance bulletin, Certificate of Conformity and Materials Certification 3.1

**Quality Control:** Quality Assurance System guarantees the control and traceability of the product.

**Rules Compliances:** CAD valve are on going to be classified for PED Directive 97/23/EC and fulfill ASME BPE Standards

**Standard design:** Shut Off bodies are available also to 180°, tangential outlet Left or Right

**Options:** For non-standard CAD Valve body Options, please contact us for further information.

**Orders and Information:** For additional information or to place a order call your nearest Distributor or visit [www.rattiinox.com](http://www.rattiinox.com)

Horizontal Assembly

